

Refurbished GE AMX-4 Plus Portable



Your Partner In Imaging

Features

- Structural reinforcements
- All worn and broken parts replaced
- Current upgrades and FMI's
- Column +/- 270 degree rotation
- Horizontal arm rebuilt
- All bearings replaced as necessary
- Rebuilt Base assembly
- Latch upgrade
- Upgraded Charger Board
- AMX 4 Plus HV cables
- AMX 4 Plus main cables
- Noise suppressors
- Base anti-static grounding cable
- New hand switch with new cable
- Chassis reinforcement
- New collimator cable
- New rotor cable
- New Super Flex HV Cables
- Collimator rebuilt
- Cross-hair window replaced
- New arm lock
- New batteries charge cycled
- Main frame chassis reinforcement installed
- All bearings replaced as necessary
- New bumper pads
- New hospital grade cord cap with cord
- New 28 Amp/hour batteries
- Factory set light to x-ray calibration
- Variable speed drive calibrated
- Complete system calibration
- Complete cosmetic repairs and refinishing
- Complete service documentation

Technical Specifications

- High frequency generator.
- GE AMX-4 Collimator
- 100 mA constant.
- 24 kVp stations.
- kVp 50-125.
- 30 mAs stations.
- mAs 0.4-320.
- LED display.
- Rotating Anode X-Ray tube
- MX-75 275kHU Focal spot .75mm
- Variable speed motor drive
- Electric solenoid locks

Refurbishing Process

At EDI we take pride in our refurbishing processes. Each and every AMX-4 Plus portable goes through a stringent process of refurbishing. After completion, every unit is given a complete electronic calibration in the factory prior to shipping. The AMX is the most reliable

portable on the market. For over twenty years, hospitals have relied on the dependability of the GE-AMX-4 portables for their imaging needs. The EDI process guarantees that each AMX-4 Plus refurbished at our facility will operate like new and be functional for many years to come.



Eastern Diagnostic Imaging
597 Winthrop Street
Taunton, MA 02780
508-828-2970, Fax: 508-828-2973
www.easterndiagnostic.com